



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L1430RW Recp Single WT 30A 125/250V 3P4W H/L YI *Eaton Wiring Devices*

Catalog Number	L1430RW
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Watertight Locking Receptacle, #18-10 Awg, 30A, Industrial, 125/250V, Back Wiring, Yellow, Steel, Single, Watertight, L14-30, Three-Pole, Four-Wire, Thermoplastic, 0.43 to 1.15 In, Ip67
Weight per unit	10.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

dimensions	6.7500 IN X 4.2500 IN X 4.0000 IN
media	Yes

### Descriptions

Description	RECP SINGLE WT 30A 125/250V 3P4W H/L YL
extra long description	EWD L1430RW Recp Single WT 30A 125/
Features	Eaton's Arrow Hart watertight locking devices utilize a unique, robust design and superior materials to provide watertight security in harsh environments.
Long Description	Eaton Arrow Hart watertight locking receptacle, #18-10 AWG, 30A, Industrial, 125/250V, Back wiring, Yellow, Steel, Single, Watertight, L14-30, Three-pole, Four-wire, Thermoplastic, 0.43 to 1.15 in, IP67
Product Type	Recp Single WT 30A 125/250V 3P4W H/L YI
Special Features	Watertight locking

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00040893687780
Manufacturers Part Number	L1430RW
UPC	040893687780

### Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Watertight

### Packaging

Carton	1
Package	10
Weight Per each	10



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility - OtherCommercial /  
Institutional Buildings / Structures - Commercial / Institutional  
Buildings / Structures - Other

standard

UL Listed,cULus Listed,CSA certified,NOM,Federal Specifications  
Classification W-C375