



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L145T848G840DX2G 14.5W Led T8 48" 40K DBL/SNGL Ended - Non-Coated *Keystone Technologies*

Catalog Number	L145T848G840DX2G
Manufacturer	Keystone Technologies
Description	14.5W Led T8 Tube, Gen 2, Glass Construction, 4FT, 4000K, 120-277V Input, 25 PCS Carton, Direct Drive, Single or Double Ended Wiring.
Weight per unit	0.6400 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	14.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	14.5W LED T8 48" 40K DBL/SNGL ENDED - NON-COATED
extra long description	Key KT-LED14.5T8-48G-840-DX2 /G2 14
Long Description	14.5W LED T8 Tube, Gen 2, Glass Construction, 4ft, 4000K, 120-277V Input, 25 pcs Carton, Direct Drive, Single or Double Ended Wiring.
Product Type	14.5W Led T8 Tube, Gen 2, Glass Construction, 4FT, 4000K, 120



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654150024
Manufacturers Part Number	KT-LED14.5T8-48G-840-DX2 /G2
UPC	843654150024

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.64

Uses, Certifications, and Standards

Energy Star	N
-------------	---