



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L15T848GC840DX2G 15W Led T8 48" 40K DBL/SNGL Ended Coated Glass G2

Keystone Technologies

Catalog Number	L15T848GC840DX2G
Manufacturer	Keystone Technologies
Description	14.5W Led T8 Tube, Gen 2, Shatter-Proof Coated Glass Contruction, 4FT, 4000K, 120-277V Input, 25 PCS Carton, Direct Drive, Single or Double Ended Wiring.
Weight per unit	0.6600 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	15
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	15W LED T8 48" 40K DBL/SNGL ENDED COATED GLASS G2
extra long description	Key KT-LED15T8-48GC-840-DX2 /G2 14.
Long Description	14.5W LED T8 Tube, Gen 2, Shatter-Proof Coated Glass Contruction, 4ft, 4000K, 120-277V Input, 25 pcs Carton, Direct Drive, Single or Double Ended Wiring.
Product Type	14.5W Led T8 Tube, Gen 2, Shatter-Proof Coated Glass Contruc



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654150079
Manufacturers Part Number	KT-LED15T8-48GC-840-DX2 /G2
UPC	843654150079

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.66

## Uses, Certifications, and Standards

Energy Star	N
-------------	---