



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1620R Turnlok SGL Recp 4W 20A 3P 480V

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | L1620R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlock Single Receptacle, 20 A, 480 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back Wire Connection, Receptacle, 3.3 In Length, Nylon Material, Black, Impact Resistant, 0.2400 LB |
| Weight per unit | 0.2404 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|--------------------|
| amperage rating | 20 |
| indoor/outdoor | Indoor |
| Outlet Type | Indoor, Commercial |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 480 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Black |
| Finish | Matte |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | TURNLOK SGL RECP 4W 20A 3P 480V |
| extra long description | P&S L1620R TURNLOK SGL REC 4W 20A 3 |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007162059 |
| Manufacturers Part Number | L1620R |
| UPC | 785007162059 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.2404 |

Uses, Certifications, and Standards

| | |
|----------|---------------|
| Mounting | Receptacle |
| standard | CULUS, UL 498 |