Pass and Seymour
20A NEMA L1820 Single Receptacle
Part No. L1820R



Receptacle Single 4-Wire 20A 120/208Volt Turnlok®

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007182057	Country Of Origin	Mexico
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in

Product Height US	2.29 in

Additional Information

Product Environmental Profile	Yes

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	4	Amperage	20 A
Number of Poles	4-Way	Wire Size	18 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L18-20R
Wire Connection Type	Screw Terminals	Voltage	120/208 V