



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1830R R SGL 4W 30A120/208V T/L

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | L1830R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Receptacle Single 4-Wire 30A 120/280VOLT Turnlok® |
| Weight per unit | 0.2400 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---------|
| amperage rating | 30 |
| Number of Wires | 4 |
| Phase | 3 |
| Poles | 4-Way |
| Voltage | 120.0 V |
| Voltage Rating | 120/208 |
| Wire Size | 18 - 10 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | R SGL 4W 30A120/208V T/L |
| extra long description | P&S L1830R R SGL 4W30A120/208V T/L |
| Long Description | Receptacle Single 4-Wire 30A 120/280volt Turnlok® |
| Product Type | R SGL 4W30A120/208V T/L |
| Special Features | Turnlock, locking device, quick thread assembly, rounded back contour, impact & corrosion resistant, new design external cord grips |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | Pass & Seymour/Legrand |
| GTIN | 00785007183054 |
| Manufacturers Part Number | L1830-R |
| UPC | 785007183054 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | RECEPTACLE |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.24 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------|
| Application | Commercial |
| nema rating | L18-30R |
| standard | CULUS, UL 498 |