



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L2130C Turnlok Conn 5W 30A 3P 120/208V

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | L2130C |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlok Registered Connector 5-Wire 30A 3-Phase 120/208V |
| Weight per unit | 0.4400 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|------------|
| amperage rating | 30 |
| Number of Wires | 5.0 |
| Phase | Three |
| Poles | 3-way |
| Voltage Rating | 120/208 |
| Wire Size | 18 - 0 AWG |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | TURNLOK CONN 5W 30A 3P 120/208V |
| extra long description | P&S L2130C TURNLOK CONN 5W 30A 3PHA |
| Long Description | Turnlok Registered Connector 5-Wire 30A 3-Phase 120/208V |
| Product Type | Turnlok Conn 5W 30A 3PHASE 120/208V |
| Special Features | Corrosion resistant turnlock locking device |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007213010 |
| Manufacturers Part Number | L2130-C |
| UPC | 785007213010 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Turnlock Connector |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.44 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------|
| Application | Industrial |
| nema rating | L21-30R |
| standard | FEDSPEC, CULUS, UL 498, FEDSPEC |