



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L25.5T5H048GC850 25W Led T5HO 48" 50K Ballast Compatible Glass *Keystone Technologies*

Catalog Number	L25.5T5H048GC850
Manufacturer	Keystone Technologies
Description	25.5W Led T5HO Tube, Shatter-Proof Coated Glass, Ballast Compatible, 4, 5000K, Smartdrive
Weight per unit	0.4800 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	3300
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	25.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G5
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	25W LED T5HO 48" 50K GLS
extra long description	Key KT-LED25.5T5HO-48GC-850-S-CP 25
Long Description	25.5W LED T5HO TUBE, SHATTER-PROOF COATED GLASS, BALLAST COMPATIBLE, 4, 5000K, SMARTDRIVE
Product Type	25W, 3200 Lumen, 4', 240' Beam Angle, Ballast Compatible, DL



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949013137
Manufacturers Part Number	KT-LED25.5T5HO-48GC-850-S /G2
UPC	890949013137

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.48

Uses, Certifications, and Standards

Energy Star	N
-------------	---