



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L2N38 #2 3/8" 2 Hole Long Barrel Compression Lug

*Nsi Industries*

Catalog Number	L2N38
Manufacturer	Nsi Industries
Description	2 Hole Long Barrel Copper Compression Lug 2 Awg - 3/8" - 1" Mounting Spacing Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. Allows Easy Inspection Of The Termination to Assure Complete Cable Insertion. Tin-Plated to Provide Corrosion and Low Contact Resistance. Marked With Die Index and Color Coded. Listed For 35KV Maximum When Properly Installed. Rated 600V. Culus 486A/B Listed. UL467 Listed On Sizes 6 Awg - 3/0 Awg. Temperature Rating 90 Degrees C.
Weight per unit	0.0900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	# 2 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Brown
Finish	Tin Plated

### Dimensions and Weight

Size	L=3.07 - W=.600 - OD=.420 - ID=.310
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	#2 3/8" 2 HOLE LONG BARREL COMPRESSION LUG
extra long description	NSI L2N-38 CU CMP Lug Long 2 AWG 3/
Features	2 Hole Long Barrel Copper Compression Lug 2 AWG - 3/8" - 1" Mounting Spacing Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Long Description	2 Hole Long Barrel Copper Compression Lug 2 AWG - 3/8" - 1" Mounting Spacing Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Product Type	Cu CMP Lug Long 2 Awg 3/8 Bolt 1 Spac
Special Features	# 2 AWG (STR) - 3/8 Mounting Holes - 1 Hole Spacing

## Manufacturer Information

Brand	NSi
GTIN	00662381035059
Manufacturers Part Number	L2N-38
UPC	662381035059

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - Two Hole

## Packaging

Carton	1
Package	50
Weight Per each	0.09

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)