



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L6N14 #6 2H Copper Lug *Nsi Industries*

| | |
|------------------|--|
| Catalog Number | L6N14 |
| Manufacturer | Nsi Industries |
| Description | 2 Hole Long Barrel Copper Compression Lug 6 Awg - 1/4" Bolt - 1" Mounting Hole Spacing Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. Allows Easy Inspection Of The Termination to Assure Complete Cable Insertion. Tin-Plated to Provide Corrosion and Low Contact Resistance. Marked With Die Index and Color Coded. Listed For 35KV Maximum When Properly Installed. Rated 600V. Culus 486A/B Listed. UL467 Listed On Sizes 6 Awg - 3/0 Awg. Temperature Rating 90 Degrees C. |
| Weight per unit | 0.0400 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|---------------|
| Cable Size | # 6 AWG (STR) |
| Material | Copper |
| Number of Holes | 2 |
| Stud Size | 1/4 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Blue |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|-------------------------------------|
| Size | L=2.36 - W=.420 - OD=.300 - ID=.200 |
|------|-------------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | #6 2H COPPER LUG |
| extra long description | NSI L6N-14 CU CMMP Lug Long 6 AWG 1 |
| Features | 2 Hole Long Barrel Copper Compression Lug 6 AWG - 1/4" Bolt - 1" Mounting Hole Spacing Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C. |
| Long Description | 2 Hole Long Barrel Copper Compression Lug 6 AWG - 1/4" Bolt - 1" Mounting Hole Spacing Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C. |
| Product Type | Cu CMMP Lug Long 6 Awg 1/4 Bolt 5/8 Spac |
| Special Features | # 6 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381035004 |
| Manufacturers Part Number | L6N-14 |
| UPC | 662381035004 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Long Barrel - Two Hole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.04 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| Mounting | 1/4 Mounting Holes |
| standard | UL486A/B, UL467 (8 AWG -3/0 AWG) |