



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L7XR6 6" Ic/Non-Ic Air-Tight Housing

Lithonia Lighting - Acuity

Catalog Number	L7XR6
Manufacturer	Lithonia Lighting - Acuity
Description	Recessed Incandescent Housings For 2X8 New Construction. Approved For Direct Burial In Insulation and All Ceiling and Wiring Types.
Weight per unit	3.4 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Hardware	Yes
Lamp Included	NO
Lamp Type	Halogen, Incandescent, LED - Static
Material	Steel
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Round
Voltage Rating	120
Warranty	1

Dimensions and Weight

Height	6.875
Length	17
Width	13.875

Descriptions

Construction	New Construction
Description	6" IC/NON-IC AIR-TIGHT HOUSING
extra long description	LITH L7X R6 6 IN air-tight, IC/Non-
Features	Design Select
Long Description	Recessed incandescent housings for 2x8 new construction. Approved for direct burial in insulation and all ceiling and wiring types.
Product Type	Downlight

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231091906
Manufacturers Part Number	L7X R6
UPC	784231091906

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

aperture size 6 in

Packaging

Carton 1

Weight 2

Weight Per each 3.35

Uses, Certifications, and Standards

Application Hospitality, Residential, Retail

environmental conditions Indoor

Mounting Recessed

standard cUL