



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LAMA500386Y 1BRL Alcu Lug *Panduit Corporation*

|                  |   |
|------------------|---|
| Catalog Number   | LAMA500386Y   |
| Manufacturer     | Panduit Corporation   |
| Description      | One-Hole, Aluminum, Single Barrel Lug, Type Lama, 4 Awg - 500 Kcmil, 3/8 (9.5MM) Stud Hole. |
| Weight per unit  | 1.7 (lbs/each)  |
| Product Category | Tools & Testers   |

### Features

|                 |                     |
|-----------------|---------------------|
| amperage rating | NA                  |
| Material        | Tin-Plated Aluminum |
| Number of Holes | 1                   |
| Stud Size       | 3/8                 |
| Voltage Rating  | 35                  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1BRL ALCU LUG   |
| extra long description | PAN LAMA500-38-6Y Pan-Lug™ LAMA500-   |
| Long Description       | One-hole, aluminum, single barrel lug, type LAMA, 4 AWG - 500 kcmil, 3/8 (9.5mm) stud hole. |
| Product Type           | Pan-Lug™ LAMA500-38-6Y Mech Con, One Hole Lug, Tin PLT Al, O                                |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | PANDUIT        |
| GTIN                      | 00074983596164 |
| Manufacturers Part Number | LAMA500-38-6Y  |
| UPC                       | 074983596164   |

### Taxonomies, Classifications, and Categories

|                      |                |
|----------------------|----------------|
| Category Description | SPLIT BOLTS    |
| Type                 | Mechanical Lug |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 1.66 |

### Uses, Certifications, and Standards

|          |   |
|----------|---|
| standard | cULus and CSA certified for use up to 600V and temperature rated to 90C |
|----------|---|