



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBY55 90D Capped Elbow *Crouse-Hinds*

Catalog Number	LBY55
Manufacturer	Crouse-Hinds
Description	Service Entrance Elbow, 1-1/2 In Trade Size, Lby Model, Electro Galvanized and Aluminum Acrylic Paint, 4-1/2 In Height, 3-3/8 In Diameter, 3.2 LB/Ea
Weight per unit	3.2 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	3.3800 IN X 3.3800 IN X 4.5000 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Descriptions

Description	90D CAPPED ELBOW
extra long description	CRS-H LBY55 1 1/2 LBY ELBOW CVR
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274277097
UPC	782274277097

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	ELBOW

Packaging

Carton	1
Weight Per each	3.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure

Class I Div 1 2 Group C D, Class II Div 1 Group E F G, Class II Div 2
Group F G, Class III

standard

UL 886, CSA C22.2