



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCCXF614BL Flex Lug, Flared, Long Barrel, 6AWG 2H 1/4\"X3/4\" Panduit Corporation

Catalog Number	LCCXF614BL
Manufacturer	Panduit Corporation
Description	Pan-Lug, Flex Lug, Grounding Application, Copper Conductor Material, 1/4 In For Stud Size, For Use With Flexible, Extra-Flexible, and Code Stranded Copper Conductors , Non-Insulated, #6 Awg Maximum Conductor Size, +90 °C Maximum Operating Temperature, 2000 V Maximum Voltage Rating, 2.61 In Overall Length, 50 PK Package Quantity, Tin Plated to Inhibit Corrosion, Color Coded Barrel, Inspection Window, Beveled Wire Entry, Csa Listed;Rohs Compliant;UI Listed, Compression Lug Terminal Type, 35 KV Voltage Rating
Weight per unit	0.0320 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	FLEX LUG, FLARED, LONG BARREL, 6AWG 2H 1/4\"X3/4\"
-------------	--

Manufacturer Information

Brand	PANDUIT
GTIN	00074983699773
Manufacturers Part Number	LCCXF6-14B-L
UPC	074983699773

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
----------------------	-----------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	50
Weight Per each	0.032