



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCCXF814AL 8AWG LB Flex Comp Lug Panduit Corporation

Catalog Number	LCCXF814AL
Manufacturer	Panduit Corporation
Description	Pan-Lug, Compression Lug, Grounding Application, Copper Conductor Material, 1/4 In For Stud Size, For Use With Flexible, Extra-Flexible, and Code Stranded Copper Conductors , Non-Insulated, #8 Awg Maximum Conductor Size, +90 °C Maximum Operating Temperature, 2000 V Maximum Voltage Rating, 2.10 In Overall Length, 50 PK Package Quantity, Tin Plated to Inhibit Corrosion, Color Coded Barrel, Inspection Window, Beveled Wire Entry, Csa Listed;Rohs Compliant;UI Listed, Compression Lug Terminal Type, 35 KV Voltage
Weight per unit	0.0220 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Stud Size	1/4
-----------	-----

Material, Color, and Finish

Color	Red
-------	-----

Descriptions

Description	8AWG LB FLEX COMP LUG
extra long description	PAN LCCXF8-14A-L Pan-Lug™ LCCXF8-14

Manufacturer Information

Brand	PANDUIT
GTIN	00074983699353
Manufacturers Part Number	LCCXF8-14A-L
UPC	074983699353

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Compression Lug

Packaging

Carton	1
Package	50
Weight Per each	0.022

Uses, Certifications, and Standards

Mounting	15/16
standard	C22.2 No. 65-13, 486A-486B File #E52164