



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LCD214AQ 2AWG 2HOLE Lug *Panduit Corporation*

|                  |  |
|------------------|--|
| Catalog Number   | LCD214AQ   |
| Manufacturer     | Panduit Corporation  |
| Description      | Standard Barrel Lug, #2 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Brown (Code) Insulation Color, +90 °C Operating Temperature, 2.40 In Overall Length, Tongue Terminal, 35 KV, 2 LB/Ea |
| Weight per unit  | 2.0 (lbs/each)   |
| Product Category | Large Terminals & Connectors   |

### Features

|                 |                   |
|-----------------|-------------------|
| Material        | Tin-Plated Copper |
| media           | Yes               |
| Number of Holes | 2                 |
| Stud Size       | 1/4               |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Brown |
|-------|-------|

### Dimensions and Weight

|      |             |
|------|-------------|
| Size | #2 AWG Code |
|------|-------------|

### Descriptions

|                        |                                    |
|------------------------|------------------------------------|
| Description            | 2AWG 2HOLE LUG                     |
| extra long description | PAN LCD2-14A-Q Pan-Lug™ LCD2-14A-Q |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983382989 |
| UPC   | 074983382989   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Compression Lug                   |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 25 |
| Weight Per each | 2  |

### Uses, Certifications, and Standards

|          |  |
|----------|--|
| Mounting | 15/16  |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, NEBS Level 3 |