



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCD214DQ 2AWG 2HOLE Lug *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | LCD214DQ |
| Manufacturer | Panduit Corporation |
| Description | Two-Hole, Standard Barrel Lug With Window, #2 Awg Wire, 1/4 Stud Hole, 1 Hole Spacing. |
| Weight per unit | 0.1052 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| media | Yes |
| Number of Holes | 2 |
| Stud Size | 1/4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Brown |
|-------|-------|

Dimensions and Weight

| | |
|------|-------------|
| Size | #2 AWG Code |
|------|-------------|

Descriptions

| | |
|------------------------|---|
| Description | 2AWG 2HOLE LUG |
| extra long description | PAN LCD2-14D-Q Pan-Lug™ LCD2-14D-Q |
| Long Description | Two-hole, standard barrel lug with window, #2 AWG wire, 1/4 stud hole, 1 hole spacing. |
| Product Type | Pan-Lug™ LCD2-14D-Q Copper Compression Connectors - Lugs |
| Special Features | Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983383009 |
| Manufacturers Part Number | LCD2-14D-Q |
| UPC | 074983383009 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Compression Lug |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0.1052 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------|--|
| Mounting | 15/16 |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, NEBS Level 3 |