



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD12.5T848GC835D 12.5W Led T8 48" 35K 120-277V *Keystone Technologies*

Catalog Number	LD12.5T848GC835D
Manufacturer	Keystone Technologies
Description	12.5W Led T8 Tube, Shatter-Proof Coated Glass, Internal Driver, 4 FT., 3500K, 120-277V Input, 25 PCS Cartons, Individually Sleeved
Weight per unit	0.7000 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1700
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	12.5W LED T8 48" 35K 120-277V
extra long description	Key KT-LED12.5T8-48GC-835-D-CP 12.5
Long Description	12.5W LED T8 TUBE, SHATTER-PROOF COATED GLASS, INTERNAL DRIVER, 4 FT., 3500K, 120-277V INPUT, 25 PCS CARTONS, INDIVIDUALLY SLEEVED
Product Type	12.5W, 1850 Lumen, 4', 240' Beam Angle, Ballast Bypass, DLC



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949003671
Manufacturers Part Number	KT-LED12.5T8-48GC-835-D-CP
UPC	890949003671

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.7

Uses, Certifications, and Standards

Energy Star	N
-------------	---