



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD12T5H024GC835D *Delisted* 12W 120-277V 35K Led T5 *Keystone Technologies*

Catalog Number	LD12T5H024GC835D
Manufacturer	Keystone Technologies
Description	12W Led T5 Tube, Shatter-Proof Coated Glass, Internal Driver, 2 FT., 3500K, 120-277V Input
Weight per unit	0.2800 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1500
Nominal Length	24 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

Material, Color, and Finish

Base Type	G5
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

Descriptions

Construction	N/A
Description	12W 120-277V 35K LED T5
extra long description	Key KT-LED12T5HO-24GC-835-D-CP 12W
Long Description	12W LED T5 Tube, Shatter-Proof coated Glass, Internal Driver, 2 ft., 3500K, 120-277V Input
Product Type	12W Led T5 Tube, Shatter-Proof Coated Glass, Internal Driver



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949016060
Manufacturers Part Number	KT-LED12T5HO-24GC-835-D-CP
UPC	890949016060

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.28

Uses, Certifications, and Standards

Energy Star	Y
-------------	---