



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD40T8H096G840D2 40W Led T8HO 96" 40K Line Volt DBL CNTCT 5550L GLS *Keystone Technologies*

Catalog Number	LD40T8H096G840D2
Manufacturer	Keystone Technologies
Description	40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 4000K, 120-277V Input, Internal Driver, Direct Drive
Weight per unit	1.3 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5500
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	40
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	40W LED T8HO 96" 40K LINE VOLT DBL CNTCT 5550L GLS
extra long description	Key KT-LED40T8HO-96G-840-D2 40W LED
Long Description	40W LED T8 Lamp, 8 long, Glass Construction, R17d HO Base, 4000K, 120-277V Input, Internal Driver, Direct Drive
Product Type	40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 4

Manufacturer Information

Brand	Keystone
GTIN	00843654140063
Manufacturers Part Number	KT-LED40T8HO-96G-840-D2
UPC	843654140063



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	10
Weight Per each	1.3

Uses, Certifications, and Standards

Energy Star	N
-------------	---