



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

SYLVANIA

LED10T8L48FG841S 10W Led T8 48" 41K FRST (Obsolete-Gen 9 Available)

Sylvania-Ledvance

Catalog Number	LED10T8L48FG841S
Manufacturer	Sylvania-Ledvance
Description	OBS79546 4FT Substitube Led T8, Frosted Glass, 10W, 82CRI, 1600 Lumen, 4100K, 60000 Life
Weight per unit	0.8560 (lbs/each)
Product Category	Lighting

Features

average life	60000
Base	G13
Lamp Type	LED T8
Shape	T8
Wattage	10.00

Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

Dimensions and Weight

Size	1.02
------	------

Descriptions

Description	10W LED T8 48" 41K FRST (OBSOLETE-GEN 9 AVAILABLE)
extra long description	SYL LED10T8L48FG841SUBG7/79546 LED1
Long Description	OBS79546 4ft SubstiTUBE LED T8, frosted glass, 10W, 82CRI, 1600 Lumen, 4100K, 60000 life
Product Type	LED10T8L48FG841SUBG7 10/CS 1/Sku

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135795466
Manufacturers Part Number	LED10T8L48FG841SUBG7/79546
UPC	046135795466

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	10
Weight Per each	0.856

Uses, Certifications, and Standards

standard	cULus
----------	-------