



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED11A190827 11W Led A19 27K Dim 1100LM 80cri

Keystone Technologies

Catalog Number	LED11A190827
Manufacturer	Keystone Technologies
Description	A19 Omni-Directional Bulb, 75W Equivalent, E26 Medium Base, 2700K, 80 Cri
Weight per unit	0.1700 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	230 Deg
Circuit Type	N/A
Input Voltage	120V
ip rating	N/A
lumens	1100
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	3
Wattage	11
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>80 Deg
color temperature	2700
housing color	N/A

Descriptions

Construction	N/A
Description	11W LED A19 27K DIM 1100LM 80CRI
extra long description	Key KT-LED11A19-O-827 75W Equiv., 1
Long Description	A19 Omni-Directional Bulb, 75W Equivalent, E26 Medium Base, 2700K, 80 CRI
Product Type	75W Equiv., 11W, 1100 Lumen, A19, E26, =80 Cri, Dimmable 27K

Manufacturer Information

Brand	Keystone
GTIN	00843654126579
Manufacturers Part Number	KT-LED11A19-O-827
UPC	843654126579



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Packaging

Carton 1

Package 60

Weight Per each 0.17

Uses, Certifications, and Standards

Energy Star Y