



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED12A19DIM0840U 12W Led A19 40K Dim 1100LM *Sylvania-Ledvance*

| | |
|------------------|---|
| Catalog Number | LED12A19DIM0840U |
| Manufacturer | Sylvania-Ledvance |
| Description | Led A19, 12W, Dimmable, 80CRI, 1100 Lumen, 4000K, 15000 Life, E26 Medium Base, Frosted Finish |
| Weight per unit | 0.3270 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|------------|
| average life | 15000 |
| Base | E26 Medium |
| Lamp Type | LED A19 |
| lumens | 1,100 |
| Shape | A19 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 12.00 |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| color rendering index (cri) | 80 |
| Style | A-shape |

Dimensions and Weight

| | |
|------|------|
| Size | 2.36 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 12W LED A19 40K DIM 1100LM |
| extra long description | SYL LED12A19DIMO840URP/41191 LED12A |
| Long Description | LED A19, 12W, Dimmable, 80CRI, 1100 Lumen, 4000K, 15000 Life, E26 Medium Base, FROSTED Finish |
| Product Type | LED12A19DIMO840URP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135411915 |
| Manufacturers Part Number | LED12A19DIMO840URP/41191 |
| UPC | 046135411915 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
|----------------------|------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.327 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|