



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED12BR40DIM930T 12W Led BR40 30K Dim 1100LM *Sylvania-Ledvance*

Catalog Number	LED12BR40DIM930T
Manufacturer	Sylvania-Ledvance
Description	Led Natural Truwave BR40, 12.5W, Dimmable, 90CRI, 1100 Lumen, 3000K, 15000 Life, Medium Base, Frosted Finish
Weight per unit	0.6132 (lbs/each)
Product Category	Lighting

### Features

average life	15000
Base	E26 Medium
beam angle	105
Lamp Type	LED BR40
lumens	1,100
Shape	BR40
Voltage	120.00 V
Voltage Rating	120.00
Wattage	12.00

### Material, Color, and Finish

color rendering index (cri)	90
color temperature	3000
Style	BR40-Shape

### Dimensions and Weight

Size	4.8
------	-----

### Descriptions

Description	12W LED BR40 30K DIM 1100LM
extra long description	SYL LED12.5BR40DIM930TLRP2/40786 LE
Long Description	LED Natural TruWave BR40, 12.5W, Dimmable, 90CRI, 1100 Lumen, 3000K, 15000 Life, Medium Base, Frosted Finish
Product Type	LED12.5BR40DIM930TLRP2 12/CS 2/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135407864
Manufacturers Part Number	LED12BR40DIM930TLRP2/40786
UPC	046135407864

### Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
----------------------	------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	0.6132

## Uses, Certifications, and Standards

standard	RoHS
----------	------