



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED12D380W383040 12W Led PAR38 30K 40' BM SPRD

Ge By Current Lamps

Catalog Number	LED12D380W383040
Manufacturer	Ge By Current Lamps
Description	Ge Led Lamps, 12 WTT, 1050 LM, 3000 K, 87.5 Cri, Dimmable, PAR38, Medium Screw Base, 5.31 In Length, 25000 HR Average Life
Weight per unit	1.1 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

average life	25000
Base	Medium Screw
dimmable	True
lumens	1050
Shape	PAR38
Wattage	12

Material, Color, and Finish

Color	White
Color Rendering Index	87.5

Dimensions and Weight

Diameter	40
Overall Length	5.31

Descriptions

Description	12W LED PAR38 30K 40' BM SPRD
extra long description	GEL LED12D38OW383040 92973 Directio
Long Description	GE LED Lamps, 12 WTT, 1050 LM, 3000 K, 87.5 CRI, Dimmable, PAR38, Medium Screw Base, 5.31 IN Length, 25000 HR Average Life
Product Type	92973 Directional Led Lamps

Manufacturer Information

Brand	GE Current
GTIN	00043168929738
Manufacturers Part Number	LED12D38OW383040
UPC	043168929738

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
----------------------	---------------------

Packaging

Carton	1
Package	6
Weight Per each	1.1117



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Indoor and outdoor Floodlight