



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED12T836GC850D 12W Led T8 36" 5K Line Voltage *Keystone Technologies*

Catalog Number	LED12T836GC850D
Manufacturer	Keystone Technologies
Description	12W Led T8 Tube, Shatter-Proof Coated Glass, Internal Driver, 3, 5000K, 120-277V Input, 25 PCS Cartons, Individually Sleeved
Weight per unit	0.5500 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1500
Nominal Length	36 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	12W LED T8 36" 5K LINE VOLTAGE
extra long description	Key KT-LED12T8-36GC-850-D-CP 12W, 1
Long Description	12W LED T8 TUBE, SHATTER-PROOF COATED GLASS, INTERNAL DRIVER, 3, 5000K, 120-277V INPUT, 25 PCS CARTONS, INDIVIDUALLY SLEEVED
Product Type	12W, 1300 Lumen, 3', 240' Beam Angle, Ballast Bypass, DLC 4.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949009321
Manufacturers Part Number	KT-LED12T8-36GC-850-D-CP
UPC	890949009321

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.55

## Uses, Certifications, and Standards

Energy Star	N
-------------	---