



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED12T8L36FG841 3' 12W Led T8 41K DBL End Line Volt 120-277V 1450L *Sylvania-Ledvance*

Catalog Number	LED12T8L36FG841
Manufacturer	Sylvania-Ledvance
Description	3 FT, Ledlescent Ballast Free Led T8, Frosted Glass, 12W, 120 277V, 82 Cri, 1450 Lumens, 4100K CCT, 50000 Life
Weight per unit	0.4490 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Medium Bipin
lumens	1,450
Shape	T8
Voltage	120.00 - 277.00 V
Wattage	12.00

Material, Color, and Finish

color rendering index (cri)	82
-----------------------------	----

Dimensions and Weight

Size	1.02
------	------

Descriptions

Description	3' 12W LED T8 41K DBL END LINE VOLT 120-277V 1450L
extra long description	SYL LED12T8L36FG841BFG2/41738 LED12
Long Description	3 ft, LEDlescent Ballast free LED T8, frosted glass, 12W, 120 277V, 82 CRI, 1450 Lumens, 4100K CCT, 50000 life
Product Type	LED12T8L36FG841BFG2 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135417382
Manufacturers Part Number	LED12T8L36FG841BFG2/41738
UPC	046135417382

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	25
Weight Per each	0.449