



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED13A190840 13W Led A19 40K Dim 1600LM 80cri

Keystone Technologies

Catalog Number	LED13A190840
Manufacturer	Keystone Technologies
Description	A19 Omni-Directional Bulb, 100W Equivalent, E26 Medium Base, 4000K, 80 Cri
Weight per unit	0.2860 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	230 Deg
Circuit Type	N/A
Input Voltage	120V
ip rating	N/A
lumens	1600
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	3
Wattage	13
Wire Type	N/A

Material, Color, and Finish

Base Type	E26
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	13W LED A19 40K DIM 1600LM 80CRI
extra long description	Key KT-LED13A19-O-840 100W Equiv.,
Long Description	A19 Omni-Directional Bulb, 100W Equivalent, E26 Medium Base, 4000K, 80 CRI
Product Type	100W Equiv., 16W, 1600 Lumen, A21, E26, =80 Cri, Dimmable 27

Manufacturer Information

Brand	Keystone
GTIN	00843654130279
Manufacturers Part Number	KT-LED13A19-O-840
UPC	843654130279



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Packaging

Carton 1

Package 60

Weight Per each 0.286

Uses, Certifications, and Standards

Energy Star Y