



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED13BR40DIM8271 13W Led BR40 27K 900LM *Sylvania-Ledvance*

Catalog Number	LED13BR40DIM8271
Manufacturer	Sylvania-Ledvance
Description	Led BR40, 12W, Dimmable, 80CRI, 900 Lumen, 2700K, 11000 Life
Weight per unit	0.6000 (lbs/each)
Product Category	Led Reflector Gu, MR R Shape L

Features

Base	E26 Medium
Lamp Type	LED BR40
lumens	900
Voltage	120.00 V
Voltage Rating	120.00
Wattage	13.00

Material, Color, and Finish

color rendering index (cri)	80
-----------------------------	----

Dimensions and Weight

Size	5.96
------	------

Descriptions

Description	13W LED BR40 27K 900LM
extra long description	SYL LED13BR40DIM82710YVRP2/79498 LE
Long Description	LED BR40, 12W, Dimmable, 80CRI, 900 Lumen, 2700K, 11000 life

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135794988
Manufacturers Part Number	79498
UPC	046135794988

Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
----------------------	------------------------------------

Packaging

Carton	1
Package	6
Weight Per each	0.6

Uses, Certifications, and Standards

standard	RoHS
----------	------