



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED13BR40DIM8301 BR40 13W 80CRI 900 Lumen 3K Dimmable Led *Sylvania-Ledvance*

Catalog Number	LED13BR40DIM8301
Manufacturer	Sylvania-Ledvance
Description	Led BR40, 12W, Dimmable, 80CRI, 900 Lumen, 3000K, 11000 Life
Weight per unit	0.5025 (lbs/each)
Product Category	Led Reflector Gu, MR R Shape L

### Features

average life	11000
Base	E26 Medium
beam angle	110
dimmable	Yes
Lamp Type	LED BR40
lumens	900
Shape	BR40
Voltage	120.00 V
Voltage Rating	120.00
Wattage	13.00

### Material, Color, and Finish

color rendering index (cri)	80
color temperature	3000

### Dimensions and Weight

Size	5.96
------	------

### Descriptions

Description	BR40 13W 80CRI 900 LUMEN 3K DIMMABLE LED
extra long description	SYL LED13BR40/DIM/830/10YV/RP2/4033
Long Description	LED BR40, 12W, Dimmable, 80CRI, 900 Lumen, 3000K, 11000 life
Product Type	LED13BR40DIM83010YVRP2 12/CS 2/Sku

### Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135403385
Manufacturers Part Number	LED13BR40/DIM/830/10YV/RP2/403
UPC	046135403385

### Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
----------------------	------------------------------------

### Packaging

Carton	1
Package	12
Weight Per each	0.5025



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

standard

FTC

---