



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED14BDT8G4840 14W Led T8 48" 40K DBL Ended Line Voltage - Glass

Ge By Current Lamps

Catalog Number	LED14BDT8G4840
Manufacturer	Ge By Current Lamps
Description	Led Type B Double Ended T8 Glass Tube
Weight per unit	0.5300 (lbs/each)
Product Category	Shape & Circular Lamps

Descriptions

Description	14W LED T8 48" 40K DBL ENDED LINE VOLTAGE - GLASS
extra long description	DOUBLE ENDED, BALLAST BYPASS, B TYPE; 48 INCH; UL, DLC APPROVAL; DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 14 WATT WATTAGE; LED GLASS TUBE; G13 BASE TYPE; 50000 LIFE IN HOUR; GLASS BASE MATERIAL; T8 SHAPE DESIGNATION; 1800 LUMEN INTENSITY; 4000; 80 COLOR RENDERING INDEX; ROHS COMPLIANT; POWER FACTOR GREATER THAN 0.9
Long Description	LED TYPE B DOUBLE ENDED T8 GLASS TUBE
Product Type	Linear Fluorescent Led Lamp

Manufacturer Information

Brand	Ge Led Lamps
GTIN	10043168394984
Manufacturers Part Number	LED14BDT8G4840
UPC	043168394987

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	20
Weight Per each	0.53