



GE
Lighting

94936 - GE LED A21 75W Replacement

LED14DA21/827W

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	A21
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Base	E26
Bulb Shape	A21

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	79
Initial Lumens-nominal	1100 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	94936
Description	LED14DA21/827W
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	14 W



GE
Lighting

94936 - GE LED A21 75W Replacement

LED14DA21/827W

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	A21
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Base	E26
Bulb Shape	A21

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	79
Initial Lumens-nominal	1100 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	94936
Description	LED14DA21/827W
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	14 W