



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED15ET8840V6P *Delisted* 15W Led T8 48" 40K Glass 1800LM 36000HR

Ge By Current Lamps

Catalog Number	LED15ET8840V6P
Manufacturer	Ge By Current Lamps
Description	T8 Led Lamp, Omni-Directional Beam Angle, 80, 4000 K, 1800 LM Brightness (Lumens), 15 W, 120 V, Glass Material, 36000 H Average Life, G13 Base, Dimmable, 48 In Length, Bypass Ballast
Weight per unit	0.8000 (lbs/each)
Product Category	Shape & Circular Lamps

Features

amperage rating	45.7
average life	36000
Fixture Type	Linear Fluorescent Fixture
lumens	1750
Voltage Rating	120

Material, Color, and Finish

color rendering index (cri)	80+
-----------------------------	-----

Dimensions and Weight

Size	48
------	----

Descriptions

Description	*DELISTED* 15W LED T8 48" 40K GLASS 1800LM 36000HR
extra long description	GEL LED15ET8/840-V6P Integrtd 4ft V
Special Features	Features: Each LED tube is outfitted with an internal GE driver, Easy disposal, Non-Hazardous Waste, No UV

Manufacturer Information

Brand	GE Current
GTIN	00043168359009
UPC	043168359009

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	LED Tube Light

Packaging

Carton	1
Package	6
Weight Per each	0.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

Plug-in
UL