



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED15T848GC835X 15W Led T8 48" 35K Combo *Keystone Technologies*

Catalog Number	LED15T848GC835X
Manufacturer	Keystone Technologies
Description	Linear Fluorescent Led Lamp, Linear, Single Ended, Instant Start Type; 47.5 Inch; UI (Canada and Us), UI, NSF/Ansi, DLC Approval; Food Equipment, Splash Zone, Dry and Damp Location Application: 120 to 277 Volt Voltage Rating; 1 Inch Diameter
Weight per unit	0.7200 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Beam Spread Angle	220 Degree
Glass Finish	FROSTED
Intensity	1800 LUMEN
Item	LED Tube
Voltage Rating	120 to 277 Volt
Wattage	15 Watt

### Material, Color, and Finish

Base Type	G13 Medium 2-Pin
Color Rendering Index	80 A
Color Temperature in Kelvin	3500

### Dimensions and Weight

Diameter	1 INCH
Length	47.5 Inch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	RoHS Compliant; Shatter Proof Coated Glass; System Wattage 18.5 Watt; Efficacy 100 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F
Commodity Description	Led Linear Fluorescent Straight, U-Shape & Circular Lamps
Description	15W LED T8 48" 35K COMBO
extra long description	LINEAR, SINGLE ENDED, INSTANT START TYPE; 47.5 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; FOOD EQUIPMENT, SPLASH ZONE, DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1 INCH DIAMETER; 15 WATT WATTAGE; LED TUBE; G13 MEDIUM 2-PIN BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 1800 LUMEN INTENSITY; 3500; 80 COLOR RENDERING INDEX; FROSTED GLASS FINISH; 220 DEGREE BEAM SPREAD ANGLE; COMBODRIVE BRAND; ROHS COMPLIANT; SHATTER PROOF COATED GLASS; SYSTEM WATTAGE 18.5 WATT; EFFICA
Long Description	LINEAR FLUORESCENT LED LAMP, LINEAR, SINGLE ENDED, INSTANT START TYPE; 47.5 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; FOOD EQUIPMENT, SPLASH ZONE, DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1 INCH DIAMETER
Product Type	Linear Fluorescent Led Lamp

## Manufacturer Information

Brand	Keystone Technologies
Manufacturers Part Number	KT-LED15T8-48GC-835-X
Model	800

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Linear, Single Ended, Instant Start

## Packaging

Carton	25
Weight Per each	0.72

## Uses, Certifications, and Standards

Application	Food Equipment, Splash Zone, Dry and Damp Location
Approval	UL (Canada and US), UL, NSF/ANSI, DLC