



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE
COMING
SOON

LED15T8L48FGDIM 15W Led T8 41K Glass Type A 2200LM

Sylvania-Ledvance

Catalog Number	LED15T8L48FGDIM
Manufacturer	Sylvania-Ledvance
Description	4FT Substitube Led T8 Value, Frosted Glass, 15W, 82 Cri, 2200 Lumens, 4100K, 50, 000 HRS Life, Dimmable
Weight per unit	0.4670 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	G13
lumens	2,200
Shape	T8
Voltage	120.00 V
Voltage Rating	120.00
Wattage	15.00

Material, Color, and Finish

color rendering index (cri)	82
-----------------------------	----

Dimensions and Weight

Size	1.02
------	------

Descriptions

Description	15W LED T8 41K GLASS TYPE A 2200LM
extra long description	SYL LED15T8L48FGDIM841SUBG9/41828 L
Long Description	4ft SubstiTUBE LED T8 Value, Frosted Glass, 15W, 82 CRI, 2200 Lumens, 4100K, 50,000 hrs Life, Dimmable
Product Type	LED15T8L48FGDIM841SUBG9 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135418280
Manufacturers Part Number	LED15T8L48FGDIM841SUBG9/41828
UPC	046135418280

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	25
Weight Per each	0.467