



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED15T8L48FGIS84 \*Delisted\* 15W Led T8 41K Glass Type A 2200LM

*Sylvania-Ledvance*

Catalog Number	LED15T8L48FGIS84
Manufacturer	Sylvania-Ledvance
Description	OBS48FGDIM841SUBG9 4FT Substitube Led T8 Value Instant Start Only, Frosted Glass, 15W, 82CRI, 2200 Lumen, 4100K, 50000 Life
Weight per unit	0.4780 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Base	G13
Lamp Type	LED T8
lumens	2,200
Shape	T8
Voltage	120.00 - 277.00 V
Wattage	15.00

### Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

### Dimensions and Weight

Size	1.02
------	------

### Descriptions

Description	*DELISTED* 15W LED T8 41K GLASS TYPE A 2200LM
extra long description	SYL LED15T8L48FGIS841SUBG9/40641 LE
Long Description	OBS48FGDIM841SUBG9 4ft SubstiTUBE LED T8 VALUE Instant Start Only, frosted glass, 15W, 82CRI, 2200 Lumen, 4100K, 50000 life
Product Type	LED15T8L48FGIS841SUBG9 25/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135406416
Manufacturers Part Number	LED15T8L48FGIS841SUBG9/40641
UPC	046135406416

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	25
Weight Per each	0.478

## Uses, Certifications, and Standards

standard	RoHS
----------	------