



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED15T8UFP841BF *Delisted* Led U Bend 4100K Ballast Free *Sylvania-Ledvance*



Catalog Number	LED15T8UFP841BF
Manufacturer	Sylvania-Ledvance
Description	OBS40614 Led T8 Ubend Curvalume Ledlescent, 15W, 82CRI, 2100 Lumen, 4100K, 50000 Life
Weight per unit	0.5440 (lbs/each)
Product Category	Shape & Circular Lamps

Features

average life	50000
Base	G13
Lamp Type	LED T8
lumens	2,100
Shape	T8
Voltage	120.00 - 277.00 V
Wattage	15.00

Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

Dimensions and Weight

Size	1.02
------	------

Descriptions

Description	*DELISTED* LED U BEND 4100K BALLAST FREE
extra long description	SYL LED15T8/U/FP/841/BF/40614 LED15
Long Description	OBS40614 LED T8 UBEND Curvalume LEDlescent, 15W, 82CRI, 2100 Lumen, 4100K, 50000 life
Product Type	LED15T8UFP841BF 10/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135406140
Manufacturers Part Number	LED15T8/U/FP/841/BF/40614
UPC	046135406140

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.544

Uses, Certifications, and Standards

standard	RoHS
----------	------