



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED15WPAR38FL830 15W Led PAR38 30K Dim

Eiko LTD

Catalog Number	LED15WPAR38FL830
Manufacturer	Eiko LTD
Description	Features: Litespanled Wet Location PAR38 Flood 40 Degree Beam 15W - 1250LM Dimmable 80+Cri 120VAC E26
Weight per unit	0.5500 (lbs/each)
Product Category	Led Parabolic Reflector Par SH

Features

average life	25,000
Base	Medium Screw (E26)
beam angle	40°
lumens	1,250
Shape	PAR38
Voltage Rating	120
Wattage	15

Material, Color, and Finish

Color	K
color rendering index (cri)	80
color temperature	3000

Dimensions and Weight

Size	4.72 DIA X 5.16
------	-----------------

Descriptions

Description	15W LED PAR38 30K DIM
extra long description	EIKO LED15WPAR38/FL/830-DIM-G8 LITE
Long Description	Features: LITESPANLED WET LOCATION PAR38 FLOOD 40 DEGREE BEAM 15W - 1250LM DIMMABLE 80+CRI 120VAC E26
Product Type	Litespanled Wet Location PAR38 Flood 40
Special Features	Suitable for Wet Locations

Manufacturer Information

Brand	Eiko
GTIN	00031293099907
Manufacturers Part Number	LED15WPAR38/FL/830-DIM-G8
UPC	031293099907

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
----------------------	---------------------

Packaging

Carton	1
Weight Per each	0.55



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

cULus, Energy Star, FCC
