



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED18T8U6GC850D 18W Led T8 U-Bend 6" 50K Line Voltage

Keystone Technologies

Catalog Number	LED18T8U6GC850D
Manufacturer	Keystone Technologies
Description	18W Led T8 Tube. Shatter-Proof Coated Glass, 120-277V Input: Direct Drive, 6" U-Bend, 5000K, 12 PCS Carton, Carton Pack
Weight per unit	0.5100 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2150
Nominal Length	6 U-Bend
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	18
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	18W LED T8 U-BEND 6" 50K LINE VOLTAGE
extra long description	Key KT-LED18T8-U6GC-850-D-CP 18W, 2
Long Description	18W LED T8 Tube. Shatter-Proof Coated Glass, 120-277V Input: Direct Drive, 6" U-Bend, 5000K, 12 pcs Carton, Carton Pack
Product Type	18W, 2200 Lumen, 6" U-Bend, 220' Beam Angle, Ballast Bypass,

Manufacturer Information

Brand	Keystone
GTIN	00890949012536
Manufacturers Part Number	KT-LED18T8-U6GC-850-D-CP
UPC	890949012536



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	12
--------	----

Weight Per each	0.51
-----------------	------

Uses, Certifications, and Standards

Energy Star	N
-------------	---