



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED21T848P2S84 4' 21W Led Signhero 40K 360 Deg BLST Bypass

*Keystone Technologies*

Catalog Number	LED21T848P2S84
Manufacturer	Keystone Technologies
Description	Led Sign Lamp, Linear, Double Sided Type; 48 Inch; UI 48/879A, UI (Canada and Us), Sam Approval; Single or Double Sided Outdoor Signage Application; 120 to 277 Volt Voltage Rating; 1.1 Inch Diameter; 21 Watt Wattage; Led Sign Tube
Weight per unit	0.3900 (lbs/each)
Product Category	Led Specialty Lamps & Modules

### Features

Beam Spread Angle	360 Degree
Intensity	2500 Lumen
Item	LED Sign Tube
Voltage Rating	120 to 277 Volt
Wattage	21 Watt

### Material, Color, and Finish

Base Material	Plastic
Base Type	R17d Rotatable
Color Rendering Index	80 A
Color Temperature in Kelvin	4000

### Dimensions and Weight

Diameter	1.1 Inch
Length	48 INCH



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Efficacy 119 Lumen per Watt; Operating Temperature -22 to 131 Deg F
Commodity Description	LED SPECIALTY LAMPS & MODULES
Description	4' 21W LED SIGNHERO 40K 360 DEG BLST BYPASS
extra long description	LINEAR, DOUBLE SIDED TYPE; 48 INCH; UL 48/879A, UL (CANADA AND US), SAM APPROVAL; SINGLE OR DOUBLE SIDED OUTDOOR SIGNAGE APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1.1 INCH DIAMETER; 21 WATT WATTAGE; LED SIGN TUBE; R17D ROTATABLE BASE TYPE; 50000 LIFE IN HOUR; PLASTIC BASE MATERIAL; 2500 LUMEN INTENSITY; 4000; 80 COLOR RENDERING INDEX; 360 DEGREE BEAM SPREAD ANGLE; SIGN HERO BRAND; EFFICACY 119 LUMEN PER WATT; OPERATING TEMPERATURE -22 TO 131 DEG F; 800 MODEL
Long Description	LED SIGN LAMP, LINEAR, DOUBLE SIDED TYPE; 48 INCH; UL 48/879A, UL (CANADA AND US), SAM APPROVAL; SINGLE OR DOUBLE SIDED OUTDOOR SIGNAGE APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1.1 INCH DIAMETER; 21 WATT WATTAGE; LED SIGN TUBE
Product Type	Led Sign Lamp

## Manufacturer Information

Brand	Keystone Technologies
GTIN	00843654132235
Manufacturers Part Number	KT-LED21T8-48P2S-840-D /G2
Model	800
UPC	843654132235

## Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	Linear, Double Sided

## Packaging

Carton	1
Package	9
Weight Per each	0.39

## Uses, Certifications, and Standards

Application	Single or Double Sided Outdoor Signage
Approval	UL 48/879A, UL (Canada and US), SAM