



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED25PAR38H0DIM 25W Led PAR38 50K Dim 2650LM *Sylvania-Ledvance*



| | |
|------------------|---|
| Catalog Number | LED25PAR38H0DIM |
| Manufacturer | Sylvania-Ledvance |
| Description | Led PAR38, 23W, Dimmable, 81CRI, 2650 Lumen, 5000K, 25000 Life, Medium Base |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | Led Parabolic Reflector Par SH |

Features

| | |
|----------------|------------|
| average life | 25000 |
| Base | E26 Medium |
| Lamp Type | LED PAR38 |
| lumens | 2,650 |
| Shape | PAR38 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 25.00 |

Material, Color, and Finish

| | |
|-----------------------------|-------------|
| color rendering index (cri) | 81 |
| Style | PAR38-shape |

Dimensions and Weight

| | |
|------|------|
| Size | 0.19 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 25W LED PAR38 50K DIM 2650LM |
| extra long description | SYL LED25PAR38HODIM850FL40WRP/74794 |
| Long Description | LED PAR38, 23W, Dimmable, 81CRI, 2650 Lumen, 5000K, 25000 Life, Medium Base |
| Product Type | LED25PAR38HODIM850FL40WRP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135747946 |
| Manufacturers Part Number | LED25PAR38HODIM850FL40WRP/7479 |
| UPC | 046135747946 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | LED PAR SHAPE LAMPS |
|----------------------|---------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 1.4516 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|