



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED26T8120P1S865 10' 26W Led Signhero 65K 180DEG BLST Bypass

Keystone Technologies

Catalog Number	LED26T8120P1S865
Manufacturer	Keystone Technologies
Description	120IN Led Sign Tube, 6500K, Single Sided Output and Rotatable R17D End Caps, 26W, 120-277V Input
Weight per unit	3.1 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	3200
Nominal Length	120 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	26
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	6500
housing color	N/A

Descriptions

Construction	N/A
Description	10' 26W LED SIGNHERO 65K 180DEG BLST BYPASS
extra long description	Key KT-LED26T8-120P1S-865-D /G2 120
Long Description	120IN LED SIGN TUBE, 6500K, SINGLE SIDED OUTPUT AND ROTATABLE R17D END CAPS, 26W, 120-277V INPUT
Product Type	120", 26W, 3, 200 Lumens, 180' Beam Spread, Single Sided Lamp

Manufacturer Information

Brand	Keystone
GTIN	00843654132860
Manufacturers Part Number	KT-LED26T8-120P1S-865-D /G2
UPC	843654132860



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 9

Weight Per each 3.11

Uses, Certifications, and Standards

Energy Star N