



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED27HIDEX39850D 27W Led Hid RPL 50K 120-277V *Keystone Technologies*

Catalog Number	LED27HIDEX39850D
Manufacturer	Keystone Technologies
Description	Led Lamp, Non-Dimmable, Hid Replacement Led, 1ST Generation, Instant Start Type; 8.35 Inch; UI (Canada and Us), DLC Approval; Enclosed Fixture Application; 120 to 277 Volt Ac Voltage Rating; 3.43 Inch Diameter
Weight per unit	1.9 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Current Rating	0.23 Amp at 120 Volt AC, 0.1 Amp at 277 Volt AC
Intensity	3830 Lumen
Item	LED Lamp
Voltage Rating	120 to 277 Volt AC
Wattage	27 Watt

Material, Color, and Finish

Base Type	Ex39 Mogul
Color Rendering Index	83
Color Temperature in Kelvin	5000

Dimensions and Weight

Diameter	3.43 INCH
Length	8.35 Inch

Descriptions

Additional Information	RoHS Compliant; Equivalent Wattage 100 Watt; Efficacy 142 Lumen per Watt; Enclosure IP64; Visible Light Area 360 Degree; Temperature -20 to 140 Deg F
Commodity Description	LED SPECIALTY LAMPS & MODULES
Description	27W LED HID RPL 50K 120-277V
Long Description	LED LAMP, NON-DIMMABLE, HID REPLACEMENT LED, 1ST GENERATION, INSTANT START TYPE; 8.35 INCH; UL (CANADA AND US), DLC APPROVAL; ENCLOSED FIXTURE APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 3.43 INCH DIAMETER
Product Type	Led Lamp



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone Technologies
Manufacturers Part Number	KT-LED27HID-EX39-850-D
Model	800

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	Non-Dimmable, HID Replacement LED, 1st Generation, Instant Start

Packaging

Carton	1
Weight Per each	1.93

Uses, Certifications, and Standards

Application	Enclosed Fixture
Approval	UL (Canada and US), DLC