



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED28T864P2S865D 64" 28W Led Signhero 65K 360DEG BLST Bypass

Keystone Technologies

Catalog Number	LED28T864P2S865D
Manufacturer	Keystone Technologies
Description	64IN Led Sign Tube, 6500K, Double Sided Output and Rotatable R17D End Caps, 28W, 120-277V Input
Weight per unit	0.5100 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	3450
Nominal Length	64 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	28
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	6500
housing color	N/A

Descriptions

Construction	N/A
Description	64" 28W LED SIGNHERO 65K 360DEG BLST BYPASS
extra long description	Key KT-LED28T8-64P2S-865-D /G2 64",
Long Description	64IN LED SIGN TUBE, 6500K, DOUBLE SIDED OUTPUT AND ROTATABLE R17D END CAPS, 28W, 120-277V INPUT
Product Type	64", 28W, 3450 Lumens, 360' Beam Spread, Double Sided Lamp,

Manufacturer Information

Brand	Keystone
GTIN	00843654132280
Manufacturers Part Number	KT-LED28T8-64P2S-865-D /G2
UPC	843654132280



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 9

Weight Per each 0.51

Uses, Certifications, and Standards

Energy Star N