



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED42T896P2S840D 8' 42W Led Signhero 40K 360 Deg BLST Bypass

Keystone Technologies

Catalog Number	LED42T896P2S840D
Manufacturer	Keystone Technologies
Description	8 FT. Led Sign Tube, 4000K, Double Sided Output and Rotatable R17D End Caps, 42W, 120-277V Input
Weight per unit	0.7700 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5300
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	42
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	8' 42W LED SIGNHERO 40K 360 DEG BLST BYPASS
extra long description	Key KT-LED42T8-96P2S-840-D /G2 96",
Long Description	8 FT. LED SIGN TUBE, 4000K, DOUBLE SIDED OUTPUT AND ROTATABLE R17D END CAPS, 42W, 120-277V INPUT
Product Type	96", 42W, 5300 Lumens, 360' Beam Spread, Double Sided Lamp,

Manufacturer Information

Brand	Keystone
GTIN	00843654132334
Manufacturers Part Number	KT-LED42T8-96P2S-840-D /G2
UPC	843654132334



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 9

Weight Per each 0.77

Uses, Certifications, and Standards

Energy Star N