



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED45HIDEX39850D \*\*\*Discontinued--Gen 3 Available\*\*\* *Keystone Technologies*

Catalog Number	LED45HIDEX39850D
Manufacturer	Keystone Technologies
Description	Led Hid Lamp, 360 ° Beam Angle, >83, 5000 K, 6350 LM Brightness (Lumens), 45 W, 120 to 277 V Ac, 0.42 A @ 120 V Ac;0.18 A @ 277 V Ac, 50000+ H Average Life, EX39 Mogul Base, Non Dimmable, 3.43 In Diameter, 10.70 In Height, Instant, 5 Yr Warranty, 2.4 LB
Weight per unit	2.3 (lbs/each)
Product Category	Hid High Intensity Discharge L

### Features

Beam Spread Angle	360 Degree
Intensity	6350 Lumen
Item	LED Lamp

### Material, Color, and Finish

Color Temperature in Kelvin	5000
-----------------------------	------

### Dimensions and Weight

Length	10.7 Inch
--------	-----------

### Descriptions

Additional Information	RoHS Compliant; Equivalent Wattage 175 Watt; Efficacy 141 Lumen per Watt; Enclosure IP64; Visible Light Area 360 Degree; Temperature -20 to 140 Deg F
Commodity Description	LED SPECIALTY LAMPS & MODULES
Description	***DISCONTINUED--GEN 3 AVAILABLE***

### Manufacturer Information

Model	800
-------	-----

### Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	Non-Dimmable, HID Replacement LED, 1st Generation, Instant Start

### Packaging

Carton	1
Weight Per each	2.33

### Uses, Certifications, and Standards

Application	Bollard, Decorative Lighting, Post Top, High Bay
Approval	UL (Canada and US), UL, DLC