



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED5R20DIM930TLR 5W Led R20 30K Dim 450LM *Sylvania-Ledvance*

Catalog Number	LED5R20DIM930TLR
Manufacturer	Sylvania-Ledvance
Description	Led Natural Truwave R20, 5.5W, Dimmable, 90CRI, 450 Lumen, 3000K, 15000 Life, Medium Base, Frosted Finish
Weight per unit	0.1926 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26 Medium
beam angle	105
dimmable	Yes
Lamp Type	LED R20
lumens	450
Shape	R20
Voltage	120.00 V
Voltage Rating	120.00
Wattage	5.00

Material, Color, and Finish

color rendering index (cri)	90
color temperature	3000
Style	R20-Shape

Dimensions and Weight

Size	2.52
------	------

Descriptions

Description	5W LED R20 30K DIM 450LM
extra long description	SYL LED5R20DIM930TLRP2/40789 LED5R2
Long Description	LED Natural TruWave R20, 5.5W, Dimmable, 90CRI, 450 Lumen, 3000K, 15000 Life, Medium Base, Frosted Finish
Product Type	LED5R20DIM930TLRP2 12/CS 2/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135407895
Manufacturers Part Number	LED5R20DIM930TLRP2/40789
UPC	046135407895

Taxonomies, Classifications, and Categories

Category Description	LED REFLECTOR GU, MR R SHAPE LAMPS
----------------------	------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.1926

Uses, Certifications, and Standards

standard	CSA
----------	-----