



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LED5WB11E12830DI 5W Led B11 30K Dim Candelabra Base

Eiko LTD

Catalog Number	LED5WB11E12830DI
Manufacturer	Eiko LTD
Description	Features: Litespanled B11 250 Degree Beam 4.5W - 350LM Dimmable 3000K 80+Cri 120VAC E12
Weight per unit	0.1020 (lbs/each)
Product Category	Led Decorative C, Ca, F, G Sha

Features

average life	25,000
Base	Candelabra Screw (E12)
lumens	325
Shape	B11
Voltage Rating	120
Wattage	4.5

Material, Color, and Finish

Color	K
color rendering index (cri)	80
color temperature	3000

Dimensions and Weight

Size	1.40 DIA X 3.83
------	-----------------

Descriptions

Description	5W LED B11 30K DIM CANDELABRA BASE
extra long description	EIKO LED5WB11/E12/830-DIM-G8 LITESP
Long Description	Features: LITESPANLED B11 250 DEGREE BEAM 4.5W - 350LM DIMMABLE 3000K 80+CRI 120VAC E12
Product Type	Litespanled B11 250 Degree Beam 4.5W - 3

Manufacturer Information

Brand	Eiko
GTIN	00031293100085
Manufacturers Part Number	LED5WB11/E12/830-DIM-G8
UPC	031293100085

Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
----------------------	--

Packaging

Carton	1
Weight Per each	0.102

Uses, Certifications, and Standards

standard	cULus,Energy Star,FCC
----------	-----------------------