



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED6.5ST19DIM822 6.5W Led VNTG ST19 22K 650LM *Sylvania-Ledvance*

Catalog Number	LED6.5ST19DIM822
Manufacturer	Sylvania-Ledvance
Description	Led ST19, 7W, Dimmable, 80CRI, 590 Lumen, 2175K, 15000 Life, E26 Medium Base, Amber Finish
Weight per unit	0.3817 (lbs/each)
Product Category	Led Decorative C, Ca, F, G Sha

Features

average life	15000
Base	E26 Medium
dimmable	Yes
Lamp Type	LED ST19
lumens	590
Shape	ST19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	6.50

Material, Color, and Finish

color rendering index (cri)	80
color temperature	2175

Dimensions and Weight

Size	2.52
------	------

Descriptions

Description	6.5W LED VNTG ST19 22K 650LM
extra long description	SYL LED6.5ST19/DIM/822/VIN/G2/RP/75
Long Description	LED ST19, 7W, Dimmable, 80CRI, 590 Lumen, 2175K, 15000 Life, E26 Medium Base, AMBER Finish
Product Type	LED6.5ST19DIM822VING2RP 6/CS 1/Sku

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135753534
Manufacturers Part Number	LED6.5ST19/DIM/822/VIN/G2/RP/7
UPC	046135753534

Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
----------------------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.3817

Uses, Certifications, and Standards

standard	cULus
----------	-------