



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7DAV3827W 7W Led A19 Dim 27K

Ge By Current Lamps

Catalog Number	LED7DAV3827W
Manufacturer	Ge By Current Lamps
Description	A19 Led Lamp, 120 ° Beam Angle, 80, 2700 K, 470 LM Brightness (Lumens), 7 W, 120 V, White, Glass Material, 25000 H Average Life, E26 Medium Screw-In Base, Dimmable, 4.63 In Length
Weight per unit	0.5300 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

lumens	470
Voltage Rating	120

Dimensions and Weight

Size	117.5
------	-------

Descriptions

Description	7W LED A19 DIM 27K
extra long description	GEL LED7DAV3/827/W 14063 LED
Special Features	Color Rendering Index (CRI) 78.0, 62.0IN Bulb Diameter

Manufacturer Information

Brand	GE Current
GTIN	00043168140638
Manufacturers Part Number	LED7DAV3/827/W
UPC	043168140638

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LEDs_Replacement Lamps_A-line_A-Line Dimming

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	6
Weight Per each	0.53